










Schematic Diagram
电气原理图



面板最大厚度6.50±0.255



Installation View
安装视图



A4			
A3			
A2			
A1			
REV	DATE	REVISION DESCRIPTION	ISSUE




COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT

MM

PROJECTED



PRODUCT NAME:

DRAWN BY

FUYUAN

CHECKED BY

COCO

MODEL NO: TP91207G224RS

DATE

2019

APPROVAL B

ALEN

Https: www.rocpcu.tw

ROCPCU TECHNOLOGY CO.,LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission

	A	B	C	D	E	F	G				
1	性能参数			13.	Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃						
	1. Heating current: Ui: AC250V, Ith: 3A 发热电流: Ui: AC250V, Ith: 3A			14.	Compression torque: ≤ 3N 按压扭力: ≤3N						
	2. Rated current:2A/DC36V 额定电流:2A/DC36V			15.	Electrical life: 100000 cycles 电气寿命: 100000 cycles						
	3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min			16.	mechanical: 5000000cycles 机械寿命: 5000000cycles						
2	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ			17.	Operation method:Self compound 操作方式: 自复式						
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ			18.	NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N						
	6. Pressing stroke:1.80mm ± 0.10 按压行程:1.80mm ± 0.10			19.	LED lamp power consumption: 20m以下 LED灯功耗: 20m以下						
	7. Contact stroke:0.60mm±0.10 接触行程 :0.60mm±0.10			20.	LED lamp lifespan: 40000h LED寿命: 40000h						
	8. welding temperature: 320 ℃± 20 ℃ 焊接温度: 320 ℃± 20 ℃			21.	LED color: Red LED颜色: 红色						
	9. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration										
3	10. Nut assembly torque:5-14N 螺帽装配力矩:5-14N										
	11. Protection level:IP65 防护等级:IP65										
	12. Explosion prevention level: IK08 防暴等级: IK08										
4											
5	A4				COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:
	A3						DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91207G224RS
	A2				X.XX ± 0.10		DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
	A1				X.X ± 0.15		ROCPCU TECHNOLOGY CO.,LTD				
	REV	DATE	REVISION DESCRIPTION ISSUE		X ± 0.25						
				ANGULAR ———		Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission					
	A	B	C	D	E	F	G				

A		B		C		D		E		F		G	
材质参数													
9		luminous zone 发光区		PC 塑料		1							
8		LEDpin LED脚		Brass 黄铜		1				Silvering 镀银			
7		Pin 引脚		Brass 黄铜		1				gold-plating 镀金			
6		Contact material 接触材质		silver alloy 银合金		1				Silvering 镀银			
5		Base 基座		PBT		1							
4		Arm nut 固定螺帽		Brass 黄铜		1				nickeling 镀镍			
3		Oring O型圈		Silica gel 硅胶		1							
2		Housing 外壳		SUS 不锈钢		1							
1		Key 按键		SUS 不锈钢		1							
NO 序号		Part name 部件名		Material 材料		QTY 数量				Remark 备注			

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:		
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91207G224RS		
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw				
A1					ROCPCU TECHNOLOGY CO.,LTD								
REV	DATE	REVISION	DESCRIPTION									ISSUE	
A		B		C		D		E		F		G	
Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission													