





A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED	PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	MODEL NO: TP91204P224RS
DATE	2019	APPROVAL B	Https: www.rocpcu.tw
ROCPCU TECHNOLOGY CO.,LTD			
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission			

	A	B	C	D	E	F	G																																																									
1	性能参数 1. Heating current: Ui: AC250V, Ith: 3A 发热电流: Ui: AC250V, Ith: 3A 2. Rated current:2A/DC36V 额定电流:2A/DC36V 3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min 4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ 5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ 6. Pressing stroke:1.80mm ± 0.10 按压行程:1.80mm ± 0.10 7. Contact stroke:0.60mm±0.10 接触行程 :0.60mm±0.10 8. welding temperature: 320 ℃± 20 ℃ 焊接温度: 320 ℃± 20 ℃ 9. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration 10. Nut assembly torque:5-14N 螺帽装配力矩:5-14N 11. Protection level:IP65 防护等级:IP65 12. Explosion prevention level: IK08 防暴等级: IK08			13. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃ 14. Compression torque: ≤ 3N 按压扭力: ≤3N 15. Electrical life: 100000 cycles 电气寿命: 100000 cycles 16. mechanical: 5000000cycles 机械寿命: 5000000cycles 17. Operation method:Self compound 操作方式: 自复式 18. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N 19. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下 20. LED lamp lifespan: 40000h LED寿命: 40000h 21. LED color: Red LED颜色: 红色				1																																																								
2				2																																																												
3				3																																																												
4				4																																																												
5				<table><tr><td>A4</td><td></td><td></td><td></td><td rowspan="5">  台普 ROCpu </td><td colspan="2">COMMON TOLERANCE</td><td>UNIT</td><td>MM</td><td>PROJCTED</td><td></td><td>PRODUCT NAME:</td></tr><tr><td>A3</td><td></td><td></td><td></td><td>DRAWN BY</td><td>FUYUAN</td><td>CHECKED BY</td><td>COCO</td><td>MODEL NO: TP91204P224RS</td></tr><tr><td>A2</td><td></td><td></td><td></td><td>DATE</td><td>2019</td><td>APPROVAL B</td><td>ALEN</td><td>Https: www.rocpu.tw</td></tr><tr><td>A1</td><td></td><td></td><td></td><td colspan="5" rowspan="2">ROCpu TECHNOLOGY CO.,LTD</td></tr><tr><td>REV</td><td>DATE</td><td>REVISION</td><td>DESCRIPTION</td><td>ISSUE</td></tr><tr><td colspan="4"></td><td colspan="8">Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission</td></tr></table>				A4				 台普 ROCpu	COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:	A3				DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91204P224RS	A2				DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw	A1				ROCpu TECHNOLOGY CO.,LTD					REV	DATE	REVISION	DESCRIPTION	ISSUE					Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission								5
A4							 台普 ROCpu	COMMON TOLERANCE		UNIT	MM		PROJCTED		PRODUCT NAME:																																																	
A3								DRAWN BY	FUYUAN	CHECKED BY	COCO		MODEL NO: TP91204P224RS																																																			
A2								DATE	2019	APPROVAL B	ALEN		Https: www.rocpu.tw																																																			
A1								ROCpu TECHNOLOGY CO.,LTD																																																								
REV				DATE	REVISION	DESCRIPTION							ISSUE																																																			
				Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission																																																												
				A	B	C	D	E	F	G																																																						

		A			B			C			D			E			F			G		
1		材质参数																		1		
2		9	luminous zone 发光区			PC 塑料			1										2			
		8	LEDpin LED脚			Brass 黄铜			1			Silvering 镀银										
		7	Pin 引脚			Brass 黄铜			1			gold-plating 镀金										
		6	Contact material 接触材质			silver alloy 银合金			1			Silvering 镀银										
3		5	Base 基座			PBT			1										3			
		4	Arm nut 固定螺帽			Brass 黄铜			1			nickeling 镀镍										
		3	Oring O型圈			Silica gel 硅胶			1													
4		2	Housing 外壳			SUS 不锈钢			1										4			
		1	Key 按键			SUS 不锈钢			1													
		NO 序号	Part name 部件名			Material 材料			QTY 数量			Remark 备注										
5		A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT		MM		PROJCTED			PRODUCT NAME:				5		
		DRAWN BY		FUYUAN					CHECKED BY		COCO		MODEL NO: TP91204P224RS									
		A3							DATE		2019		APPROVAL B		ALEN		Https: www.rocpcu.tw					
		A2							X.XX		± 0.10		ROCPCU TECHNOLOGY CO.,LTD									
		A1							X.X		± 0.15											
REV		DATE		REVISION DESCRIPTION		ISSUE		X		± 0.25		Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission										
								ANGULAR		——												
		A		B		C		D		E		F		G								