


安倍:20A 电压:300V 线径:0.2-2.5mm²
 胶壳: 尼龙66工程塑料, UL 94V-0阻燃等级
 温度: 110° C (UL), -40° C to T110° C (IEC)
 触点材料: 黄铜 (HPb59-3), 镀镍
 脚子: 黄铜 (H65) 环保
 推荐剥线长度: 6-7mm
 接线位数: 2位-24位



Technical drawing of a mechanical part showing dimensions: 5.0 XNP, 5.00, 3.10, 4.98, and a hole diameter of Ø1.40.

		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	HY128-5.0-XXP	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X. ±0.25		
			MODEL NAME	HY128-5.0-XXP			X.x ±0.20		
			3RD ANGLE PROJ	HanElectricity Co.,LTD				X.xx ±0.15	
								ANGULAR ±3°	
								FILE.NO.	