









PCB Installation Dimension Drawing
PCB安装尺寸图



The circuit principle diagram
电路原理图

- | | |
|-----------------------------------|---|
| 1. Rated voltage: 16V (DC) | 4. Withstand voltage: AC 250V (50Hz)/min |
| 1. 额定电压: 16V (DC) | 4. 耐压: AC 250V (50Hz) /min |
| Rated current: 0.5A | 5. Operating temperature: -10 °C ~ +60 °C |
| 额定电流: 0.5A | 5. 使用温度: -10 °C ~ +60 °C |
| 2. Insulation resistance: ≥ 50M Ω | 6. Action force: 100 ± 30gf |
| 2. 绝缘电阻: ≥ 50M Ω | 6. 动作力: 100 ± 30gf |
| 3. Contact resistance: ≤ 200m Ω | 7. Service life: 50000 times |
| 3. 接触电阻: ≤ 200m Ω | 7. 寿命: 50000次 |

7	Bladeterminal 定位柱	High temp thermoplastic 高温热塑性塑料	2	Black 黑色
6	Spring 基座	High temp thermoplastic 高温热塑性塑料	1	
5	Spring 弹簧	SUS	1	Black 黑色
4	Concact 接触片	Phosphor Bronze 磷青铜	1	Ag plating 镀银
3	Slider 滑块	SUS	1	
2	Cover stent 覆盖支架	High temp thermoplastic 高温热塑性塑料	1	Black 黑色
1	Handle 按柄	Phosphor bronze	1	Ag plating 镀银
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE
		A		B



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT

MM

PROJECTED



PRODUCT NAME:

DRAWN BY

FUYUAN

CHECKED BY

COCO

MODEL NO: TP73321

DATE

2019

APPROVAL B

ALEN

Https: www.rocpcu.tw

ROCPCU TECHNOLOGY CO.,LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission