

REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
AO	N/A		INITIAL RELEASE	2024.10.28

- Specifications(规格):
- 1.Impedance(特性阻抗) : 50Ω;
 - 2.Frequency (工作频率) : DC~6GHz;
 - 3.VSWR (电压驻波比) : 1.50@3GHz; 1.60@6GHz;
 - 4.Insulation resistance(绝缘阻抗) : ≥100MΩ;
 - 5.Dielectric withstand voltage (介质耐电压) : 800V AC;

- 6.Mating cycles (耐久性) : ≥25 cycles;
- 7.Engagement force(啮合力) : ≤ 25N;
- 8.Retention force latch(保持力) : ≥110N;
- 9.Temperature range(使用温度): -40℃~+105℃;

PART NO.:

XZ X X -K1M- XXXX -K1F- X X
① ② ③ ④ ⑤

① Cable TYPE:

- 3: RG174
4: 1.5DS
6: RG58
7: Dacor302
8: RG174LL
9: RG58LL

② Successive number: 1~Z

③ Length (mm): 1000=1000mm

④ Coding A: A~Z



⑤ Coding B: A~Z

接点表(Wiring Table)

A端(A port)

Cable

B端(B port)



3	Connector	FAKRA Female connector,Z Code	1SET		XKB 星城 connection	DESIGN	希文	VIEW: 	MODEL TYPE: Assembly cable, FAKRA series					
2	Connector	FAKRA Male connector,Z Code	1SET			CHECKED		UNIT: mm/in	PART NO.: XZ91-K1M-5000-K1F-ZZ					
1	Cable	RG58LL Cable PVC OD2.80mm Black,-40~105℃	1PCS			APPROVED		SIZE: A4	DWG NO.: X-XZ91-K1M-5000-K1F-ZZ					
NO.	NAME	SPEC.	Q'TY	NOTE										
www.helloxkb.com					www.helloxkb.cn					www.xk-dg.cn				
XKB INDUSTRIAL PRECISION CO.,LIMITED														
					SCALE					PAGE				
					N/A					1/1				
										REVISION				
										A0				