

REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
AO	N/A		INITIAL RELEASE	2024.10.28

- Specifications(规格):
- 1.Impedance(特性阻抗) : 50Ω;
 - 2.Frequency (工作频率) : DC~6GHz;
 - 3.VSWR (电压驻波比) : 1.50@3GHz; 1.60@6GHz;
 - 4.Insulation resistance(绝缘阻抗) : ≥100MΩ;
 - 5.Dielectric withstand voltage (介质耐电压) : 800V AC;

- 6.Mating cycles (耐久性) : ≥25 cycles;
- 7.Engagement force(啮合力) : ≤ 25N;
- 8.Retention force latch(保持力) : ≥110N;
- 9.Temperature range(使用温度): -40℃~+105℃;



PART NO.:

XZ X 3 -K1M- XXXX -K1F- X X
①② ③ ④ ⑤

- ① Cable TYPE:
3: RG174
4: 1.5DS
6: RG58
7: Dacor302
8: RG174LL
9: RG58LL
- ② Successive number: 1~Z
- ③ Length (mm): 1000=1000mm
- ④ Coding A: A~Z
- ⑤ Coding B: A~Z

接点表(Wiring Table)

A端(A port) Cable B端(B port)



4	Clip	Connector Clip: CC20SFT1712	2PCS	
3	Connector	FAKRA Female connector,Z Code	1SET	
2	Connector	FAKRA Male connector,Z Code	1SET	
1	Cable	RG174LL Cable PVC OD2.80mm Black,-40~105℃	1PCS	
NO.	NAME	SPEC.	Q'TY	NOTE

CONNEXION

希文

DESIGN

CHECKED

APPROVED

VIEW:

UNIT: mm/in

SIZE: A4

MODEL TYPE:

PART NO.:

DWG NO.:

Assembly cable, FAKRA series

XZ84-K1M-XXXX-K1F-ZZ

X-XZ84-K1M-XXXX-K1F-ZZ

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE

PAGE

REVISION