

产 品 基 本 参 数






安倍:7A     电压:250V

胶壳:  尼龙66工程塑料,    UL 94V-0阻燃等级


温度:  110° C (UL),-40° C to T110° C(IEC)

触点材料:  黄铜 (H65) 环保, 镀亮锡

接线位数: 2位-24位



PCB LAYOUT



|          |         | new          |                | 2015/5/3               |                                       | A           | 瀚源        |            |  |
|----------|---------|--------------|----------------|------------------------|---------------------------------------|-------------|-----------|------------|--|
| ECN BO.  |         | DESCRIPTION. |                | DATE.                  |                                       | REV.        |           |            |  |
| DESIGNED | CHECKED | APPROVAL     | DRAWING NUMBER |                        |                                       | SCALT: 1/2  |           | SCALE: 3:1 |  |
| Mikey    | Tom     | Jerry        | PART NAME      | 2EDGRM-3.81-XXP        | UNLESS OTHERWISE SPECIFIED,TOLERANCE: |             | X. ±0.25  |            |  |
|          |         |              | MODEL NAME     | 2EDGRM-3.81-XXP        |                                       |             | X.x ±0.20 |            |  |
|          |         |              | 3RD ANGLE PROJ | HanElectricity Co.,LTD |                                       |             |           | X.xx ±0.15 |  |
|          |         |              |                |                        |                                       | ANGULAR ±3° |           | FILE.NO.   |  |