


Single color electrical schematic diagram
单色电气原理图



Installation View
安装视图

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT

MM

PROJECTED



PRODUCT NAME:

DRAWN BY

FUYUAN

CHECKED BY

COCO

MODEL NO: TP92210P224GS

DATE

2019

APPROVAL B

ALEN

Https: www.roc pu. tw

ROC PU TECHNOLOGY CO.,LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission

	A	B	C	D	E	F	G		
1	性能参数 1. Heating current: Ui: AC250V, lth: 5A 发热电流: Ui: AC250V, lth: 5A 2. Rated current:3A/DC36V 额定电流:3A/DC36V 3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min 4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ 5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ 6. Pressing stroke:2.50mm ± 0.10 按压行程:2.50mm ± 0.10 7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10 8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N 9. Protection level:IP67 防护等级:IP67 10. Explosion prevention level: IK10 防暴等级: IK10 11. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃ 12. Compression torque: ≤ 6N 按压扭力: ≤ 6N				13. Electrical life: 100000 cycles 电气寿命: 100000 cycles 14. mechanical: 500000cycles 机械寿命: 500000cycles 15. Operation method:Self repeating form 操作方式: 自复式 16. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下 17. LED lamp lifespan: 40000h LED寿命: 40000h 18. LED color: Green LED颜色: 绿色 19. LED Lamp Voltage: 24V LED灯电压: 24V 20. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N				1
2									2
3									3
4									4
5									5

A		B		C		D		E		F		G	
材质参数													
10	luminous zone 发光区			PC 塑胶		1							
9	LEDpin LED引脚			Brass 黄铜		1		Silvering 镀银					
8	Base 底座			PA46		1							
7	Pin 引脚			Brass 黄铜		1		gold-plating 镀金					
6	Contact material 接触材质			silver alloy 银合金		1		Silvering 镀银					
5	LED Base LED底座			PC 塑胶		1							
4	Arm nut 固定螺帽			Brass 黄铜		1		nickeling 镀镍					
3	Oring O型圈			Silica gel 硅胶		1							
2	Housing 外壳			SUS 不锈钢		1							
1	Key 按键			SUS 不锈钢		1							
NO 序号	Part name 部件名			Material 材料		QTY 数量		Remark 备注					

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:		
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP92210P224GS		
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw				
A1					ROCPCU TECHNOLOGY CO.,LTD								
REV	DATE	REVISION	DESCRIPTION									ISSUE	ANGULAR
Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission													
A		B		C		D		E		F		G	