









PCB Installation Dimension Drawing
PCB 安装尺寸图



The circuit principle diagram
电路原理图



1. Rated voltage: 3V (DC)
1. 额定电压: 3V (DC)
Rated current: 10mA
额定电流: 10mA
2. Insulation resistance: $\geq 50M \Omega$
2. 绝缘电阻: $\geq 50M \Omega$
3. Contact resistance: $\leq 1 \Omega$
3. 接触电阻: $\leq 1 \Omega$

4. Action force: $30 \pm 10gf$
4. 动作力: $30 \pm 10gf$
5. Service life: 20000 times
5. 寿命: 20000次

5	Welding wire foot 焊线脚	Phosphor copper 磷铜	2	Ag plating 镀银
4	Base 基座	LCP	1	Black 黑色
3	Spring 弹簧	Phosphor copper 磷铜	1	Ag plating 镀银
2	Lid 盖子	SUS	1	
1	Handle 按柄	PA46	1	Black 黑色
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED	PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO
DATE	2019	APPROVAL B	ALLEN
MODEL NO: TP73221			
Https: www.rocpcu.tw			
ROCPUC TECHNOLOGY CO.,LTD			
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission			