










PCB Installation Dimension Drawing
PCB 安装尺寸图



The circuit principle diagram
电路原理图



1. Rated voltage: 16V (DC)
1.额定电压: 16V (DC)
Rated current: 0.5A
额定电流: 0.5A
2. Insulation resistance: $\geq 50M \Omega$
2.绝缘电阻: $\geq 50M \Omega$
3. Contact resistance: $\leq 200m \Omega$
3.接触电阻: $\leq 200m \Omega$

6. Action force: $30 \pm 10gf$
6.动作力: $30 \pm 10gf$
7. Service life: 50000 times
7.寿命: 50000次

5	Terminal 端子	Brass 黄铜	4	Ag plating 镀银
4	Base 底座	PA46	1	Black 黑色
3	Shrapnel 弹片	Phosphor copper 磷铜	1	Ag plating 镀银
2	Cover 盖子	PA46	1	Black 黑色
1	Handle 按柄	POM	1	White 白色
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE
		A		B



COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP72911
DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
ROCPCU TECHNOLOGY CO.,LTD				
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				
D	E	F	G	