










Schematic Diagram
电气原理图



Installation View
安装视图

A4				 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91204P224GS
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
REV	DATE	REVISION	DESCRIPTION		ISSUE	X					
					ANGULAR	_____	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				
	A		B		C		D	E		F	G

性能参数														
1. Heating current: Ui: AC250V, lth: 3A 发热电流: Ui: AC250V, lth: 3A														
2. Rated current:2A/DC36V 额定电流:2A/DC36V														
3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min														
4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ														
5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ														
6. Pressing stroke:1.80mm ± 0.10 按压行程:1.80mm ± 0.10														
7. Contact stroke:0.60mm±0.10 接触行程 :0.60mm±0.10														
8. welding temperature: 320 ℃± 20 ℃ 焊接温度: 320 ℃± 20 ℃														
9. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration														
10. Nut assembly torque:5-14N 螺帽装配力矩:5-14N														
11. Protection level:IP65 防护等级:IP65														
12. Explosion prevention level: IK08 防暴等级: IK08														
13. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃														
14. Compression torque: ≤ 3N 按压扭力: ≤3N														
15. Electrical life: 100000 cycles 电气寿命: 100000 cycles														
16. mechanical: 5000000cycles 机械寿命: 5000000cycles														
17. Operation method:Self compound 操作方式: 自复式														
18. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N														
19. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下														
20. LED lamp lifespan: 40000h LED寿命: 40000h														
21. LED color: Green LED颜色: 绿色														

A		B		C		D		E		F		G	
材质参数													
9		luminous zone 发光区		PC 塑料		1							
8		LEDpin LED脚		Brass 黄铜		1				Silvering 镀银			
7		Pin 引脚		Brass 黄铜		1				gold-plating 镀金			
6		Contact material 接触材质		silver alloy 银合金		1				Silvering 镀银			
5		Base 基座		PBT		1							
4		Arm nut 固定螺帽		Brass 黄铜		1				nickeling 镀镍			
3		Oring O型圈		Silica gel 硅胶		1							
2		Housing 外壳		SUS 不锈钢		1							
1		Key 按键		SUS 不锈钢		1							
NO 序号		Part name 部件名		Material 材料		QTY 数量				Remark 备注			

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:		
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91204P224GS		
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw				
A1					ROCPCU TECHNOLOGY CO.,LTD								
REV	DATE	REVISION	DESCRIPTION									ISSUE	
A		B		C		D		E		F		G	
Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission													