




PCB.soldering team
PCB.焊接板




circuit diagram
电路图



SPECIFICATION

规范
Rating: 50mA.12V DC
额定值: 50mA.12V DC
Insulation resistance: ≥100MΩ
绝缘电阻: ≥100MΩ
Dielectric strength: ≥250V AC 1 min
抗电强度: ≥250V AC 1 min



Contact resistance: ≤100mΩ max
接触电阻: ≤100mΩ max
Travel: 0.20±0.1mm
行程: 0.20±0.1mm
Lifetime: 300000 times
寿命: 300000 times
Operating force: 260±50gf
操作力: 260±50gf

6	Stem 按钮	Brass 黄铜	1	Acid pickling 酸洗
5	Cover plate 盖板	SUS	1	Clean 清洗
4	Dustproof film 防尘膜	Poly 聚酰亚胺	1	Orange 橙黄色
3	Shrapnel 弹片	SUS	1	Silvering 镀银
2	Essence 本体	PPA	1	Black 黑色
1	Card 卡件	Brass 黄铜	1	Silvering 镀银
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:		
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP15822618		
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw		
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD						
REV	DATE	REVISION	DESCRIPTION		ISSUE	X						± 0.25	
					ANGULAR	_____	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission						
A		B			C		D		E		F		G