

REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A0	N/A		INITIAL RELEASE	2024.10.28

- Specifications(规格):
- 1.Impedance(特性阻抗) : 50Ω;
 - 2.Frequency (工作频率) : DC~6GHz;
 - 3.VSWR (电压驻波比) : 1.50@3GHz;
 - 4.Insulation resistance(绝缘阻抗) : ≥100MΩ;
 - 5.Dielectric withstand voltage (介质耐电压) : 800V AC;

- 6.Mating cycles (耐久性) : ≥5 cycles;
- 7.Engagement force(啮合力) : ≤45N;
- 8.Retention force latch(保持力) : ≥110N;
- 9.Temperature range(使用温度): -40℃~+105℃;

PART NO.:

XZ X 3 -K1FW- XXXX -K1MW- X X
①② ③ ④ ⑤

① Cable TYPE:

- 3: RG174
4: 1.5DS
6: RG58
7: Dacor302
8: RG174LL
9: RG58LL

② Successive number: 1~Z

③ Length (mm): 1000=1000mm

④ Coding A: A~Z



⑤ Coding B: A~Z

接点表(Wiring Table)


A端(A port)

Cable

B端(B port)



4	Clip	Connector Clip: CC20SFT712	2PCS
3	Connector	FAKRA Male connector Waterproof,Z Code	1SET
2	Connector	FAKRA Female connector Waterproof,Z Code	1SET
1	Cable	RG174LL Cable PVC OD2.80mm Black,-40~105℃	
NO.	NAME	SPEC.	Q'TY



连接

DESIGN

CHECKED

APPROVED

希文

UNIT: mm/in

SIZE: A4

VIEW: 

PART NO.: XZ84-K1MW-XXXX-K1F-ZZ

DWG NO.: X-XZ84-K1MW-XXXX-K1F-ZZ

MODEL TYPE: Assembly cable,FAKRA series

SCALE: N/A

PAGE: 1/1

XKB INDUSTRIAL PRECISION CO.,LIMITED

REVISION