









Electrical principles without lights
无灯电气原理



Installation View
安装视图



A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT

MM

PROJECTED



PRODUCT NAME:

DRAWN BY

FUYUAN

CHECKED BY

COCO

MODEL NO: TP91908G1S

DATE

2019

APPROVAL B

ALEN

Https: www.rocpcu.tw

ROCPCU TECHNOLOGY CO.,LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission

	A	B	C	D	E	F	G				
1	性能参数				13. Electrical life: 500000 cycles 电气寿命: 500000 cycles						
	1. Heating current: Ui: AC250V, lth: 5A 发热电流: Ui: AC250V, lth: 5A				14. mechanical: 500000cycles 机械寿命: 500000cycles						
	2. Rated current:3A/DC36V 额定电流:3A/DC36V				15. Operation method:Self-locking 操作方式: 自锁式						
2	3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min				16. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N						
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ										
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ										
	6. Pressing stroke:3.00mm ± 0.10 按压行程:3.00mm ± 0.10										
	7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10										
	8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N										
	9. Protection level:IP67 防护等级:IP67										
3	10. Explosion prevention level: IK10 防暴等级: IK10										
	11. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃										
	12. Compression torque: ≤ 4N 按压扭力: ≤4N										
	连接形式										
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下										
4	2. Can be used with dedicated connectors: 可配专用接插件使用:										
	2.1 Switch function wire: green (C) blue wire (NO) yellow wire (NC) 开关功能线材: 绿色(C) 蓝线 (NO) 黄线 (NC)										
5	A4			 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:
	A3				DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91908G1S		
	A2				X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
	A1				X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
	REV	DATE	REVISION DESCRIPTION	ISSUE	X	± 0.25					
					ANGULAR	——	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission				
	A	B	C	D	E	F	G				

A		B		C		D		E		F		G	
材质参数													
8		Base 底座		PA46		1							
7		Pin 引脚		Brass 黄铜		1				gold-plating 镀金			
6		Contact material 接触材质		silver alloy 银合金		1				Silvering 镀银			
5		LED Base LED底座		PC 塑料		1							
4		Arm nut 固定螺帽		Brass 黄铜		1				nickeling 镀镍			
3		Oring O型圈		Silica gel 硅胶		1							
2		Housing 外壳		SUS 不锈钢		1							
1		Key 按键		SUS 不锈钢		1							
NO 序号		Part name 部件名		Material 材料		QTY 数量				Remark 备注			

A4				 台普 ROC CPU	COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:		
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91908G1S		
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw				
A1					ROC CPU TECHNOLOGY CO.,LTD								
REV	DATE	REVISION	DESCRIPTION									ISSUE	ANGULAR
Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission													
A		B		C		D		E		F		G	