


REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A0	N/A		INITIAL RELEASE	2024.10.28

- Specifications(规格):
- 1.Impedance(特性阻抗) : 50Ω;
 - 2.Frequency (工作频率) : DC~6GHz;
 - 3.VSWR (电压驻波比) : 1.50@3GHz;
 - 4.Insulation resistance(绝缘阻抗) : ≥100MΩ;
 - 5.Dielectric withstand voltage (介质耐电压) : 800V AC;
 - 6.Mating cycles (耐久性) : ≥5 cycles;
 - 7.Engagement force(啮合力) : ≤45N;
 - 8.Retention force latch(保持力) : ≥110N;
 - 9.Temperature range(使用温度): -40℃~+105℃;


PART NO.:

XZ X 2 -K1FW- XXXX -K1MW- X X
①② ③ ④ ⑤

- ① Cable TYPE:
3: RG174
4: 1.5DS
6: RG58
7: Dacor302
8: RG174LL
9: RG58LL
- ② Successive number: 1~Z
- ③ Length (mm): 1000=1000mm
- ④ Coding A: A~Z
- ⑤ Coding B: A~Z



接点表(Wiring Table)



PART NO.		Length (mm/inch)	TOLERANCES (mm/inch)
XZ82-K1FW-1000-K1MW-ZZ		1000 [39.370]	±15 [0.591]
XZ82-K1FW-1500-K1MW-ZZ		1500 [59.055]	±15 [0.591]
XZ82-K1FW-2000-K1MW-ZZ		2000 [78.740]	±20 [0.787]
XZ82-K1FW-3000-K1MW-ZZ		3000 [118.110]	±30 [1.181]
XZ82-K1FW-5000-K1MW-ZZ		5000 [196.851]	±60 [2.362]

4	Clip	Connector Clip: CC20SFT712	1PCS
3	Connector	FAKRA Male connector Waterproof,Z Code	1SET
2	Connector	FAKRA Female connector Waterproof,Z Code	1SET
1	Cable	RG174LL Cable PVC OD2.80mm Black,-40~105℃	
NO.	NAME	SPEC.	Q'TY NOTE

Connection

DESIGN	希文	VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	PART NO.:
APPROVED		SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO.,LIMITED		SCALE	PAGE
		N/A	1/1