

REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
AO	N/A		INITIAL RELEASE	2024.10.28

- Specifications(规格):
- 1.Impedance(特性阻抗) : 50Ω;
 - 2.Frequency (工作频率) : DC~6GHz;
 - 3.VSWR (电压驻波比) : 1.50@3GHz; 1.60@6GHz;
 - 4.Insulation resistance(绝缘阻抗) : ≥100MΩ;
 - 5.Dielectric withstand voltage (介质耐电压) : 800V AC;

- 6.Mating cycles (耐久性) : ≥25 cycles;
- 7.Engagement force(啮合力) : ≤ 25N;
- 8.Retention force latch(保持力) : ≥110N;
- 9.Temperature range(使用温度): -40℃~+105℃;

PART NO.:

XZ X X -K1M- XXXX -K1M- X X
①②③④⑤

① Cable TYPE:


- 3: RG174
4: 1.5DS
6: RG58
7: Dacor302
8: RG174LL
9: RG58LL

② Successive number: 1~Z


③ Length (mm): 1000=1000mm

④ Coding A: A~Z

⑤ Coding B: A~Z



接点表(Wiring Table)



PART NO.	Length (mm/inch)	TOLERANCES (mm/inch)
XZ81-K1M-500-K1M-ZZ	500 [19.685]	±10 [0.394]
XZ81-K1M-1000-K1M-ZZ	1000 [39.370]	±15 [0.591]
XZ81-K1M-1500-K1M-ZZ	1500 [59.055]	±15 [0.591]
XZ81-K1M-2000-K1M-ZZ	2000 [78.740]	±20 [0.787]
XZ81-K1M-3000-K1M-ZZ	3000 [118.110]	±30 [1.181]
XZ81-K1M-5000-K1M-ZZ	5000 [196.851]	±60 [2.362]

DESIGN				MODEL TYPE:			
DESIGN	希文	VIEW:	①	Assembly cable, FAKRA series	PART NO.:	XZ81-K1M-XXXX-K1M-ZZ	
CHECKED		UNIT: mm/in			DWG NO.:	X-XZ81-K1M-XXXX-K1M-ZZ	
APPROVED		SIZE: A4			SCALE	PAGE	REVISION
					N/A	1/1	AO

XKB INDUSTRIAL PRECISION CO., LIMITED

www.helloxkb.com www.xk-dia.com