







PCB. Welding board
PCB.焊接板



SPECIFICATION

规范

Rating: 50mA.12V DC

额定值: 50mA.12V DC

Insulation resistance: $\geq 100M\Omega$

绝缘电阻: $\geq 100M\Omega$

Dielectric strength: $\geq 250V$ AC 1 min

抗电强度: $\geq 250V$ AC 1 min

Contact resistance: $\leq 100m\Omega$ max

接触电阻: $\leq 100m\Omega$ max

Travel: $0.20 \pm 0.1mm$




行程: $0.20 \pm 0.1mm$

Lifetime: 300000 times

寿命: 300000 times

Operating force: $260 \pm 50gf$

操作力: $260 \pm 50gf$



Circuit board
电路班

6	Stem 按钮	Brass 黄铜	1	Acid pickling 酸洗
5	Cover plate 盖板	SUS	1	Clean 清洗
4	Dustproof film 防尘膜	Poly 聚酰亚胺	1	Orange 橙黄色
3	Shrapnel 弹片	SUS	1	Silvering 镀银
2	Essence 本体	LCP	1	Black 黑色
1	Card 卡件	Phosphor bronze 磷铜	1	Silvering 镀银
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE
		A		B



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP16342615
DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
ROCPCU TECHNOLOGY CO.,LTD				
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				
D	E	F	G	