





PCB. Welding board
PCB.焊接板




Circuit board
电路图



SPECIFICATION

规范
Rating: 50mA.12V DC
额定值: 50mA.12V DC
Insulation resistance: $\geq 100M\Omega$
绝缘电阻: $\geq 100M\Omega$
Dielectric strength: $\geq 250V$ AC 1 min
抗电强度: $\geq 250V$ AC 1 min



Contact resistance: $\leq 100m\Omega$ max
接触电阻: $\leq 100m\Omega$ max
Travel: $0.20 \pm 0.1mm$
行程: $0.20 \pm 0.1mm$
Lifetime: 100000 times
寿命: 100000 times
Operating force: $160 \pm 50gf$
操作力: $160 \pm 50gf$

6	Stem 按钮	Brass 黄铜	1	Acid pickling 酸洗
5	Cover plate 盖板	SUS	1	Clean 清洗
4	Dustproof film 防尘膜	Poly 聚酰亚胺	1	Orange 橙黄色
3	Shrapnel 弹片	SUS	1	Black 黑色
2	Essence 本体	PPA	1	Black 黑色
1	Card 卡件	Brass 黄铜	1	Silvering 镀银
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4			
A3			
A2			
A1			
REV	DATE	REVISION DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED	PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO
DATE	2019	APPROVAL B	ALLEN
MODEL NO: TP15921615			
Https: www.rocpcu.tw			
ROCPU TECHNOLOGY CO.,LTD			
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission			