





1




2




Circuit diagram
电路图

3



4



1. Rated voltage: 3V (DC)
1.额定电压: 3V (DC)
Rated current: 10mA
额定电流: 10mA
2. Insulation resistance: $\geq 50\text{M}\Omega$
2.绝缘电阻: $\geq 50\text{M}\Omega$
3. Contact resistance: $\leq 500\text{m}\Omega$
3.接触电阻: $\leq 500\text{m}\Omega$

4. Action force: $100 \pm 10\text{gf}$
4.动作力: $100 \pm 10\text{gf}$
5. Service life: 20000 times
5.寿命: 20000次

6	Solder leg 焊锡脚	Brass 黄铜	4	Ag plating 镀银
5	Base 底座	PA46	1	Black 黑色
4	Lid 盖子	PA46	1	Black 黑色
3	Spring 弹簧	Steel wire 钢丝	1	
2	Reed 簧片	Silvered copper 覆银铜	1	Ag plating 镀银
1	Handle 按柄	PA46	1	Black 黑色
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

5

A4					COMMON TOLERANCE		UNIT	MM	PROJECTED		PRODUCT NAME:	
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP73021	
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw	
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD					
REV	DATE	REVISION	DESCRIPTION		ISSUE	X						
					ANGULAR	——	Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission					
					A	B	C	D	E	F	G	