










Schematic Diagram
电气原理图



Installation View
安装视图

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT

MM

PROJECTED



PRODUCT NAME:

DRAWN BY

FUYUAN

CHECKED BY

COCO

MODEL NO: TP91208G224RS

DATE

2019

APPROVAL B

ALEN

Https: www.rocpcu.tw

ROC PU TECHNOLOGY CO.,LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission

	A	B	C	D	E	F	G		
1	性能参数			13. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃					
	1. Heating current: Ui: AC250V, Ith: 3A 发热电流: Ui: AC250V, Ith: 3A			14. Compression torque: ≤ 3N 按压扭力: ≤3N					
	2. Rated current:2A/DC36V 额定电流:2A/DC36V			15. Electrical life: 100000 cycles 电气寿命: 100000 cycles					
	3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min			16. mechanical: 5000000cycles 机械寿命: 5000000cycles					
2	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ			17. Operation method:Self compound 操作方式: 自复式					
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ			18. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N					
	6. Pressing stroke:1.80mm ± 0.10 按压行程:1.80mm ± 0.10			19. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下					
	7. Contact stroke:0.60mm±0.10 接触行程 :0.60mm±0.10			20. LED lamp lifespan: 40000h LED寿命: 40000h					
	8. welding temperature: 320 ℃± 20 ℃ 焊接温度: 320 ℃± 20 ℃			21. LED color: Red LED颜色: 红色					
	9. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration								
3	10. Nut assembly torque:5-14N 螺帽装配力矩:5-14N								
	11. Protection level:IP65 防护等级:IP65								
	12. Explosion prevention level: IK08 防暴等级: IK08								
4									
5	A4			台普 ROCPU COMMON TOLERANCE	UNIT	MM	PROJCTED		PRODUCT NAME:
	A3				DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91208G224RS
	A2				DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw
	A1				ROCPU TECHNOLOGY CO.,LTD				
	REV	DATE	REVISION DESCRIPTION						
	A	B	C	D	E	F	G		

A														B														C														D														E														F														G																																																							
材质参数																																																																																																																																											