

Specifications(规格):



- 1.Impedance(特性阻抗) : 100Ω;
- 2.Frequency (工作频率) : DC~2GHz;
- 3.Return Loss (回波损耗) : ≥ 20dB @1GHz;
- 4.Insulation resistance(绝缘阻抗) : ≥100MΩ;
- 5.Dielectric withstand voltage (介质耐电压) : 250V AC;
- 6.Mating cycles (耐久性) : ≥25 cycles;
- 7.Retention force latch(保持力) : ≥110N;
- 8.Temperature range(使用温度): -40℃~+105℃;

PART NO.:

XZ 5 X - H14F- XXXX -H14F-X X
①②③④⑤

- ① Cable Type: HSD 535;
- ② Successive number: 1~Z;
- ③ Length(mm): 1000=1000mm
- ④ Coding A: A~Z
- ⑤ Coding B: A~Z

Wiring Table



REV.		ECN NO.	LOCATION	REVISIONS		DESCRIPTION	DATE	DESIGN
AO		N/A				INITIAL RELEASE	2025.05.23	

DESIGN		VIEW:	MODEL TYPE:
CHECKED	Sivan	UNIT: mm/in	Assembly Cable,HSD4PIN Series
APPROVED		SIZE: A4	DWG NO.: X-XZ5D-H14F-XXXX-H14F-ZZ

SCALE	PAGE	REVISION
N/A	1/1	AO

1	Name	SPEC.	QTY	NOTE
2	Connector	HSD4P Female connecto Z Code	2SET	
1	Cable	LEONI Dacc@ 535 Cable PVC ODø4.6±0.3mm Black	1PCS	
NO.				

www.helloxkb.com www.helloxkb.cn www.xk-da.cn

XKB 连接

KKB INDUSTRIAL PRECISION CO.,LIMITED