


Specifications(规格):

- 1.Impedance(特性阻抗) : 100Ω;
- 2.Frequency (工作频率) : DC~2GHz;
- 3.Return Loss (回波损耗) : ≥ 20dB @1GHz;
- 4.Insulation resistance(绝缘阻抗) : ≥100MΩ;
- 5.Dielectric withstand voltage (介质耐电压) : 250V AC;
- 6.Mating cycles (耐久性) : ≥25 cycles;
- 7.Retention force latch(保持力) : ≥110N;
- 8.Temperature range(使用温度): -40℃~+105℃;


PART NO.:

XZ 5 X - H14FW- XXXX -H14FW-X X
①② ③ ④⑤

- ① Cable Type: HSD 535;
- ② Successive number: 1~Z;
- ③ Length(mm): 1000=1000mm
- ④ Coding A: A~Z
- ⑤ Coding B: A~Z




Wiring Table



REVISIONS			
REV.	ECN NO.	LOCATION	DESCRIPTION
A0	N/A		INITIAL RELEASE
			DATE
			2024.11.10
			DESIGN

PART NO.	Length (mm/inch)	TOLERANCES (mm/inch)
XZ5D-H14FW-500-H14FW-ZZ	500 [19.685]	±10 [0.394]
XZ5D-H14FW-1000-H14FW-ZZ	1000 [39.370]	±15 [0.591]
XZ5D-H14FW-1500-H14FW-ZZ	1500 [59.055]	±15 [0.591]
XZ5D-H14FW-2000-H14FW-ZZ	2000 [78.740]	±20 [0.787]

DESIGN			
DESIGN	Sivan	VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	PART NO.:
APPROVED		SIZE: A4	DWG NO.:
			X-XZ5D-H14FW-XXXX-H14FW-ZZ
		SCALE	PAGE
		N/A	1/1
			REVISION
			A0



XKB INDUSTRIAL PRECISION CO., LIMITED