









A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED	PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	MODEL NO: TP91920P224GS
DATE	2019	APPROVAL B	Https: www.roc pu. tw
ROCPU TECHNOLOGY CO.,LTD			
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission			

	A	B	C	D	E	F	G													
1	性能参数 1. Heating current: Ui: AC250V, lth: 5A 发热电流: Ui: AC250V, lth: 5A 2. Rated current:3A/DC36V 额定电流:3A/DC36V 3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min 4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ 5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ 6. Pressing stroke:2.50mm ± 0.10 按压行程:2.50mm ± 0.10 7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10 8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N 9. Protection level:IP67 防护等级:IP67 10. Explosion prevention level: IK10 防暴等级: IK10 11. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃ 12. Compression torque: ≤ 6N 按压扭力: ≤6N			13. Electrical life: 500000 cycles 电气寿命: 500000 cycles 14. mechanical: 500000cycles 机械寿命: 500000cycles 15. Operation method:Self repeating form 操作方式: 自复式 16. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N 17. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下 18. LED lamp lifespan: 40000h LED寿命: 40000h 19. LED color: Green LED颜色: 绿色				1												
2	连接形式 1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下 2. Can be used with dedicated connectors: 可配专用接插件使用: 2.1 1NO1NC Switch function wire: green (C) blue wire (NO) yellow wire (NC) 1NO1NC 开关功能线材: 绿色(C) 蓝线 (NO) 黄线 (NC) 2.2 2NO2NC switch function wire: green black wire (C), blue black wire (NO), yellow white wire (NC) 2NO2NC开关功能线材: 绿黑线(C)、蓝黑线 (NO)、黄白线 (NC) 2.3 LED functional wire: red wire positive pole, black wire negative pole, LED without distinction between positive and negative poles LED功能线材: 红线正极, 黑线负极, LED不分正负极							2												
3	A4 A3 A2 A1 REV DATE REVISION DESCRIPTION ISSUE 台普 ROCPU COMMON TOLERANCE X.XX ± 0.10 X.X ± 0.15 X ± 0.25 ANGULAR —— UNIT MM PROJCTED ⊕ PRODUCT NAME: DRAWN BY FUYUAN CHECKED BY COCO MODEL NO: TP91920P224GS DATE 2019 APPROVAL B ALEN Https: www.rocpu.tw ROCPU TECHNOLOGY CO.,LTD Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission							3												
4								4												
5								5												
A			B			C			D			E			F			G		

