


Specifications(规格):

- 1.Impedance(特性阻抗) : 100Ω;
- 2.Frequency (工作频率) : DC~2GHz;
- 3.Return Loss (回波损耗) : ≥ 20dB @1GHz;
- 4.Insulation resistance(绝缘阻抗) : ≥100MΩ;
- 5.Dielectric withstand voltage (介质耐电压) : 250V AC;
- 6.Mating cycles (耐久性) : ≥25 cycles;
- 7.Retention force latch(保持力) : ≥110N;
- 8.Temperature range(使用温度): -40℃~+105℃;


PART NO.:

XZ 5 X - H14M- XXXX -H14F-X X
①②③④

- ① Cable Type: HSD 535;
- ② Successive number: 1~Z;
- ③ Length(mm): 1000=1000mm
- ④ Coding A: A~Z
- ⑤ Coding B: A~Z



Wiring Table



				XZ50-H14M-ZZ		2006-11-4F-ZZ		2006-11-4F-ZZ	
				DESIGN	Sivan	VIEW:		MODEL TYPE:	Assembly Cable,HSD4PIN Series
3	Connector	HSD4P Female connector,Z code	1 SET	CHECKED		UNIT:	mm/in	PART NO.:	XZ50-H14M-XXXX-H14F-ZZ
2	Connector	HSD4P Male connector,Z code	1 SET	APPROVED		SIZE:	A4	DWG. NO.:	X-XZ50-H14M-XXXX-H14F-ZZ
1	Cable	LEONI Dacora® 535 Cable PVC ODø4.6±0.3mm Black							
NO.	Name	SPEC.	QTY	NOTE					
				www.helloxb.com www.xk-dq.cn					
				XKB 星城 Connection					
XKB INDUSTRIAL PRECISION CO.,LIMITED									
				SCALE	PAGE	REVISION			
				N/A	1/1	A0			