







Installation View
安装视图



A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED	PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	MODEL NO: TP91914P224GS
DATE	2019	APPROVAL B	Https: www.roc pu. tw

ROC PU TECHNOLOGY CO.,LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission

A		B		C		D		E		F		G	
1	性能参数											1	
	1. Heating current: Ui: AC250V, lth: 5A 发热电流: Ui: AC250V, lth: 5A												
	2. Rated current:3A/DC36V 额定电流:3A/DC36V												
2	3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min											2	
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ												
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ												
3	6. Pressing stroke:2.50mm ± 0.10 按压行程:2.50mm ± 0.10											3	
	7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10												
	8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N												
4	9. Protection level:IP67 防护等级:IP67											4	
	10. Explosion prevention level: IK10 防暴等级: IK10												
	11. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃												
5	12. Compression torque: ≤ 4N 按压扭力: ≤4N											5	
	连接形式												
	1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下												
6	2. Can be used with dedicated connectors: 可配专用接插件使用:											6	
	2.1 1NO1NCSwitch function wire: green (C) blue wire (NO) yellow wire (NC) 1NO1NC开关功能线材: 绿色(C) 蓝线 (NO) 黄线 (NC)												
	2.2 2NO2NC switch function wire: red positive pole, black negative pole, LED without distinguishing positive and negative poles 2NO2NC开关功能线材: 红色正极、黑色负极、LED不分正负极												
7	2.3 LED functional wire: red wire positive pole black wire negative pole LED without distinguishing positive and negative poles LED功能线材: 红线正极 黑线负极 LED不分正负极											7	
8	A4											8	
	A3												
	A2												
9	A1											9	
	REV												
	DATE												
10	REVISION DESCRIPTION											10	
	ISSUE												
11	COMMON TOLERANCE											11	
	UNIT												
	MM												
12	PROJECTED											12	
	DRAWN BY												
	FUYUAN												
13	CHECKED BY											13	
	COCO												
	MODEL NO: TP91914P224GS												
14	DATE											14	
	2019												
	APPROVAL B												
15	ALEN											15	
	Https: www.roc pu. tw												
	ROC PU TECHNOLOGY CO.,LTD												
16	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission											16	
17	A											17	
	B												
	C												
18	D											18	
	E												
	F												
19	G											19	

A		B		C		D		E		F		G	
材质参数													
10	luminous zone 发光区			PC 塑胶		1							
9	LEDpin LED引脚			Brass 黄铜		1		Silvering 镀银					
8	Base 底座			PA46		1							
7	Pin 引脚			Brass 黄铜		1		gold-plating 镀金					
6	Contact material 接触材质			silver alloy 银合金		1		Silvering 镀银					
5	LED Base LED底座			PC 塑胶		1							
4	Arm nut 固定螺帽			Brass 黄铜		1		nickeling 镀镍					
3	Oring O型圈			Silica gel 硅胶		1							
2	Housing 外壳			SUS 不锈钢		1							
1	Key 按键			SUS 不锈钢		1							
NO 序号	Part name 部件名			Material 材料		QTY 数量		Remark 备注					

A4				 台普 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:		
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91914P224GS		
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw				
A1					ROCPCU TECHNOLOGY CO.,LTD								
REV	DATE	REVISION	DESCRIPTION									ISSUE	
A		B		C		D		E		F		G	
Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission													