


Specifications(规格):

1. Impedance (特性阻抗) : 50Ω;
2. Frequency (工作频率) : DC~6GHz;
3. VSWR (电压驻波比) : 1.50@3GHz;
4. Insulation resistance (绝缘阻抗) : $\geq 100\text{M}\Omega$;
5. Dielectric withstand voltage (介质耐电压) : 800V AC;
6. Mating cycles (耐久性) : ≥ 5 cycles;
7. Engagement force (啮合力) : $\leq 45\text{N}$;
8. Retention force latch (保持力) : $\geq 110\text{N}$;
9. Temperature range (使用温度) :
-40℃~+105℃;


PART NO.:

$$\frac{XZ}{(1)} \frac{X}{(2)} - K1FW - \frac{XXXX}{(3)} - K1FW - \frac{X}{(4)} \frac{X}{(5)}$$

- ① Cable TYPE:
3: RG174
4: 1.5DS
6: RG58
7: Dacard302
8: RG174LL
9: RG58LL
- ② Successive number: 1~Z
- ③ Length (mm): 1000=1000mm
- ④ Coding A: A~Z
- ⑤ Coding B: A~Z



接点表(Wiring Table)



PART NO.	Length (mm/inch)	TOLERANCE (mm/inch)
XZ81-K1FW-1000-K1FW-ZZ	1000 [39.370]	±15 [0.591]
XZ81-K1FW-1500-K1FW-ZZ	1500 [59.055]	±15 [0.591]
XZ81-K1FW-2000-K1FW-ZZ	2000 [78.740]	±20 [0.787]
XZ81-K1FW-3000-K1FW-ZZ	3000 [118.110]	±30 [1.181]
XZ81-K1FW-5000-K1FW-ZZ	5000 [196.851]	±60 [2.362]

						XZ81-K1FW-5000-K1FW-ZZ	5000 [196.851]	180 [2.558]
					DESIGN	希文	VIEW: 	MODEL TYPE: Assembly cable, FAKRA series
2	Connector	FAKRA Female connector Waterproof, Z Code	2SET		CHECKED		UNIT: mm/in	PART NO.: XZ81-K1FW-XXXX-K1FW-ZZ
1	Cable	RG174LL Cable PVC OD2.80mm Black,-40~105℃	/		APPROVED		SIZE: A4	DWG. NO.: X-XZ81-K1FW-XXX-K1FW-ZZ
NO.	NAME	SPEC.	Q'TY	NOTE				
					www.helloxb.com www.xk-dg.cn			

XKB
星城

connection

XKB INDUSTRIAL PRECISION CO.,LIMITED

SCALE

PAGE

REVISION

N/A

1/1

A0