

Specifications(规格):



- 1.Impedance(特性阻抗) : 100Ω;
- 2.Frequency (工作频率) : DC~2GHz;
- 3.Return Loss (回波损耗) : ≥ 20dB @1GHz;
- 4.Insulation resistance(绝缘阻抗) : ≥100MΩ;
- 5.Dielectric withstand voltage (介质耐电压) : 250V AC;
- 6.Mating cycles (耐久性) : ≥25 cycles;
- 7.Retention force latch(保持力) : ≥110N;
- 8.Temperature range(使用温度): -40℃~+105℃;

PART NO.:

XZ 5 X -H14MW- XXXX -H14FW-X X
①② ③ ④⑤

- ① Cable Type: HSD 535;
- ② Successive number: 1~Z;
- ③ Length(mm): 1000=1000mm
- ④ Coding A: A~Z
- ⑤ Coding B: A~Z

Wiring Table



REVISIONS			
REV.	ECN NO.	LOCATION	DESCRIPTION
A0	N/A		INITIAL RELEASE
			DATE
			2024.11.10
			DESIGN

3	Connector	HSD4P Female connector, Z Code, Waterproof	1 SET	
2	Connector	HSD4P Male connector, Z Code, Waterproof	1 SET	
1	Cable	LEONI Doca® 535 Cable PVC ODø4.6±0.3mm Black		
NO.	Name	SPEC.	QTY	NOTE
www.helloxkb.com www.helloxkb.cn www.xk-dg.cn				

Connection

XKB INDUSTRIAL PRECISION CO., LIMITED			
DESIGN	Sivan	VIEW:	MODEL TYPE:
CHECKED		UNIT: mm/in	PART NO.:
APPROVED		SIZE: A4	DWG NO.:
			X-XZ5D-H14MW-XXXX-H14FW-ZZ
		SCALE	PAGE
		N/A	1/1
			REVISION
			A0