


1		2		3		4																																														
RoHS		<table><tr><th colspan="6">REVISIONS</th></tr><tr><th>REV.</th><th>ECN NO.</th><th>LOCATION</th><th>DESCRIPTION</th><th>DATE</th><th>DESIGN</th></tr><tr><td>A0</td><td>N/A</td><td></td><td>INITIAL RELEASE</td><td>2025.05.23</td><td></td></tr></table>						REVISIONS						REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN	A0	N/A		INITIAL RELEASE	2025.05.23																												
REVISIONS																																																				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE	DESIGN																																															
A0	N/A		INITIAL RELEASE	2025.05.23																																																
Specifications(规格): 1.Impedance(特性阻抗): 100Ω; 2.Frequency (工作频率): DC~2GHz; 3.Return Loss (回波损耗): ≥ 20dB @1GHz; 4.Insulation resistance(绝缘阻抗): ≥100MΩ; 5.Dielectric withstand voltage (介质耐压): 250V AC; 6.Mating cycles (耐久性): ≥25 cycles; 7.Retention force latch(保持力): ≥110N; 8.Temperature range(使用温度): -40℃~+105℃;																																																				
PART NO.: XZ <u>5</u> <u>X</u> - H16M- <u>XXXX</u> -H16F-<u>X</u> <u>X</u> ① ② ③ ④ ⑤ ① Cable Type: HSD 535; ② Successive number: 1~Z; ③ Length(mm): 1000=1000mm ④ Coding A: A~Z ⑤ Coding B: A~Z		Wiring Table <table><tr><th>A Port</th><th>CABLE</th><th>B Port</th></tr><tr><td>1</td><td>Blue</td><td>1</td></tr><tr><td>2</td><td>Orange</td><td>2</td></tr><tr><td>3</td><td>Green</td><td>3</td></tr><tr><td>4</td><td>Brown</td><td>4</td></tr><tr><td>5</td><td>Braid</td><td>5</td></tr><tr><td>6</td><td>Red</td><td>6</td></tr><tr><td>7</td><td>Black</td><td>7</td></tr></table> Shell Power GND				A Port	CABLE	B Port	1	Blue	1	2	Orange	2	3	Green	3	4	Brown	4	5	Braid	5	6	Red	6	7	Black	7																							
A Port	CABLE	B Port																																																		
1	Blue	1																																																		
2	Orange	2																																																		
3	Green	3																																																		
4	Brown	4																																																		
5	Braid	5																																																		
6	Red	6																																																		
7	Black	7																																																		
<table><tr><td>6</td><td>Clip</td><td>Connector Clip: CC20SFT712</td><td>1 PCS</td></tr><tr><td>5</td><td>Connector</td><td>HSD4+2P Male connector Z Code,带卡槽</td><td>1 SET</td></tr><tr><td>4</td><td>Connector</td><td>HSD4+2P Female connector Z Code</td><td>1 SET</td></tr><tr><td>3</td><td>Tape</td><td>Flannelette(绒布) Black</td><td></td></tr><tr><td>2</td><td>Cable</td><td>22AWG*1P (red+black) PVC OD1.60mm</td><td>1 PCS</td></tr><tr><td>1</td><td>Cable</td><td>LEONI Dacar® 535 Cable PVC ODø4.6±0.3mm Black</td><td>1 PCS</td></tr><tr><td>NO.</td><td>Name</td><td>SPEC.</td><td>Q'TY</td><td>NOTE</td></tr></table>		6	Clip	Connector Clip: CC20SFT712	1 PCS	5	Connector	HSD4+2P Male connector Z Code,带卡槽	1 SET	4	Connector	HSD4+2P Female connector Z Code	1 SET	3	Tape	Flannelette(绒布) Black		2	Cable	22AWG*1P (red+black) PVC OD1.60mm	1 PCS	1	Cable	LEONI Dacar® 535 Cable PVC ODø4.6±0.3mm Black	1 PCS	NO.	Name	SPEC.	Q'TY	NOTE	 XKB INDUSTRIAL PRECISION CO.,LIMITED <table><tr><td>DESIGN</td><td>Sivan</td><td>VIEW: </td><td>MODEL TYPE: Assembly Cable,HSD4+2PIN Series</td></tr><tr><td>CHECKED</td><td></td><td>UNIT: mm/in</td><td>PART NO.: XZ5K-H16M-XXXX-H16F-ZZ</td></tr><tr><td>APPROVED</td><td></td><td>SIZE: A4</td><td>DWG NO.: X-XZ5K-H16M-XXXX-H16F-ZZ</td></tr></table> <table><tr><td>SCALE</td><td>PAGE</td><td>REVISION</td></tr><tr><td>N/A</td><td>1/1</td><td>A0</td></tr></table>				DESIGN	Sivan	VIEW: 	MODEL TYPE: Assembly Cable,HSD4+2PIN Series	CHECKED		UNIT: mm/in	PART NO.: XZ5K-H16M-XXXX-H16F-ZZ	APPROVED		SIZE: A4	DWG NO.: X-XZ5K-H16M-XXXX-H16F-ZZ	SCALE	PAGE	REVISION	N/A	1/1	A0
6	Clip	Connector Clip: CC20SFT712	1 PCS																																																	
5	Connector	HSD4+2P Male connector Z Code,带卡槽	1 SET																																																	
4	Connector	HSD4+2P Female connector Z Code	1 SET																																																	
3	Tape	Flannelette(绒布) Black																																																		
2	Cable	22AWG*1P (red+black) PVC OD1.60mm	1 PCS																																																	
1	Cable	LEONI Dacar® 535 Cable PVC ODø4.6±0.3mm Black	1 PCS																																																	
NO.	Name	SPEC.	Q'TY	NOTE																																																
DESIGN	Sivan	VIEW: 	MODEL TYPE: Assembly Cable,HSD4+2PIN Series																																																	
CHECKED		UNIT: mm/in	PART NO.: XZ5K-H16M-XXXX-H16F-ZZ																																																	
APPROVED		SIZE: A4	DWG NO.: X-XZ5K-H16M-XXXX-H16F-ZZ																																																	
SCALE	PAGE	REVISION																																																		
N/A	1/1	A0																																																		
1		2		3		4																																														