





A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED	PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO
DATE	2019	APPROVAL B	ALEN
ROCPU TECHNOLOGY CO.,LTD			

MODEL NO: TP91202P224GS
Https: www.rocpcu.tw

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission

	A	B	C	D	E	F	G				
1	性能参数			13. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃							
	1. Heating current: Ui: AC250V, Ith: 3A 发热电流: Ui: AC250V, Ith: 3A			14. Compression torque: ≤ 3N 按压扭力: ≤3N							
	2. Rated current:2A/DC36V 额定电流:2A/DC36V			15. Electrical life: 100000 cycles 电气寿命: 100000 cycles							
2	3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min			16. mechanical: 5000000cycles 机械寿命: 5000000cycles							
	4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ			17. Operation method:Self compound 操作方式: 自复式							
	5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ			18. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N							
	6. Pressing stroke:1.80mm ± 0.10 按压行程:1.80mm ± 0.10			19. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下							
	7. Contact stroke:0.60mm±0.10 接触行程 :0.60mm±0.10			20. LED lamp lifespan: 40000h LED寿命: 40000h							
	8. welding temperature: 320 ℃± 20 ℃ 焊接温度: 320 ℃± 20 ℃			21. LED color: Green LED颜色: 绿色							
3	9. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration										
	10. Nut assembly torque:5-14N 螺帽装配力矩:5-14N										
	11. Protection level:IP65 防护等级:IP65										
	12. Explosion prevention level: IK08 防暴等级: IK08										
4											
5	A4			 台普 ROCPCU	COMMON TOLERANCE	UNIT	MM	PROJCTED		PRODUCT NAME:	
	A3					DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91202P224GS	
	A2				X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
	A1				X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD				
	REV	DATE	REVISION DESCRIPTION		ISSUE	X					
					ANGULAR	——	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission				
	A	B	C	D	E	F	G				

A														B														C														D														E														F														G																																																							
材质参数																																																																																																																																											
</																																																																																																																																											