

CrystalUnits
DT-206 DIP
Series



Features

Dimensions:2.0 x 6.0 mm

Applications

Standard Frequency:32.768KHz

RTC

Resistance Welded Type Crystal Units

Low Impedance Performance



Electrical Specifications

Item / Type	
Norminal Frequency 标称频率	32.768 KHz
Frequency Tolerance(at 25 °C) 频率偏差	± 5 ppm ± 10 ppm ± 20 ppm
Operation Temperature Range 工作温度	- 2 0 ~ + 70 °C
Shunt Capacitance (C0) 静态电容	2.0pF typical
Motional Capacitance (C1) 动态电容	3.0fF typical
Insulation Resistance (IR) 绝缘电阻	500 MΩ Min.
Drive Level (DL) 激励电平	1.0 μW Max.
Load Capacitance(CL) 负载电容	6PF , 12.5 pF ,
Turnover Temperature (Ti) 拐点温度	25 °C ± 5 °C
Parabolic Coefficient (B) 温度系数	(- 0.036 ± 0.01) * 10 ⁶ / °C ²
Aging (at 25 °C) 年老化	± 3 ppm at First year
Storage Temperature Range 储存温度	-55 ~ +125 °C

Equivalent Series Resistance(ESR)

308

35KΩ Max

Dimensions

