










PCB. Welding board  
PCB. 焊接板



Circuit board  
电路图



### SPECIFICATION

规范  
Rating: 50mA.12V DC  
额定值: 50mA.12V DC  
Insulation resistance:  $\geq 100M\Omega$   
绝缘电阻:  $\geq 100M\Omega$   
Dielectric strength:  $\geq 250V$  AC 1 min  
抗电强度:  $\geq 250V$  AC 1 min

Contact resistance:  $\leq 100m\Omega$  max  
接触电阻:  $\leq 100m\Omega$  max  
Travel:  $0.20 \pm 0.1mm$   
行程:  $0.20 \pm 0.1mm$   
Lifetime: 300000 times  
寿命: 300000 times  
Operating force:  $160 \pm 50gf$   
操作力:  $160 \pm 50gf$

|          |                       |                       |           |                     |
|----------|-----------------------|-----------------------|-----------|---------------------|
| 6        | Stem<br>按钮            | Brass<br>黄铜           | 1         | Acid pickling<br>酸洗 |
| 5        | Cover plate<br>盖板     | SUS                   | 1         | Clean<br>清洗         |
| 4        | Dustproof film<br>防尘膜 | Poly<br>聚酰亚胺          | 1         | Orange<br>橙黄色       |
| 3        | Shrapnel<br>弹片        | SUS                   | 1         | Silvering<br>镀银     |
| 2        | Essence<br>本体         | LCP                   | 1         | Black<br>黑色         |
| 1        | Card<br>卡件            | Phosphor bronze<br>磷铜 | 1         | Silvering<br>镀银     |
| NO<br>序号 | Part name<br>部件名      | Material<br>材料        | QTY<br>数量 | Remark<br>备注        |

|     |      |          |             |       |
|-----|------|----------|-------------|-------|
| A4  |      |          |             |       |
| A3  |      |          |             |       |
| A2  |      |          |             |       |
| A1  |      |          |             |       |
| REV | DATE | REVISION | DESCRIPTION | ISSUE |



### COMMON TOLERANCE

|         |            |
|---------|------------|
| X.XX    | $\pm 0.10$ |
| X.X     | $\pm 0.15$ |
| X       | $\pm 0.25$ |
| ANGULAR | —          |

|                                                                                                                                                           |        |            |      |                      |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------|--------|------------|------|----------------------|
| UNIT                                                                                                                                                      | MM     | PROJECTED  |      | PRODUCT NAME:        |
| DRAWN BY                                                                                                                                                  | FUYUAN | CHECKED BY | COCO | MODEL NO: TP16421617 |
| DATE                                                                                                                                                      | 2019   | APPROVAL B | ALEN | Https: www.rocpcu.tw |
| ROCPCU TECHNOLOGY CO.,LTD                                                                                                                                 |        |            |      |                      |
| Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission |        |            |      |                      |