



Single color electrical schematic diagram  
单色电气原理图



Installation View  
安装视图

|     |      |          |             |                                                                                                      |                  |        |                                                                                                                                                          |        |            |                                                                                       |                           |
|-----|------|----------|-------------|------------------------------------------------------------------------------------------------------|------------------|--------|----------------------------------------------------------------------------------------------------------------------------------------------------------|--------|------------|---------------------------------------------------------------------------------------|---------------------------|
| A4  |      |          |             | <br><b>ROCPCU</b> | COMMON TOLERANCE |        | UNIT                                                                                                                                                     | MM     | PROJECTED  |  | PRODUCT NAME:             |
| A3  |      |          |             |                                                                                                      |                  |        | DRAWN BY                                                                                                                                                 | FUYUAN | CHECKED BY | COCO                                                                                  | MODEL NO: TP92209P224RS   |
| A2  |      |          |             |                                                                                                      | X.XX             | ± 0.10 | DATE                                                                                                                                                     | 2019   | APPROVAL B | ALEN                                                                                  | Https:      www.rocpcu.tw |
| A1  |      |          |             |                                                                                                      | X.X              | ± 0.15 | <b>ROCPCU TECHNOLOGY CO.,LTD</b>                                                                                                                         |        |            |                                                                                       |                           |
| REV | DATE | REVISION | DESCRIPTION |                                                                                                      | ISSUE            | X      |                                                                                                                                                          |        |            |                                                                                       |                           |
|     |      |          |             |                                                                                                      | ANGULAR          | _____  | Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission |        |            |                                                                                       |                           |
|     | A    |          | B           |                                                                                                      | C                |        | D                                                                                                                                                        | E      |            | F                                                                                     | G                         |

</

|          |                          |   |  |                     |  |           |  |                    |  |   |  |   |  |
|----------|--------------------------|---|--|---------------------|--|-----------|--|--------------------|--|---|--|---|--|
| A        |                          | B |  | C                   |  | D         |  | E                  |  | F |  | G |  |
| 材质参数     |                          |   |  |                     |  |           |  |                    |  |   |  |   |  |
| 10       | luminous zone<br>发光区     |   |  | PC<br>塑胶            |  | 1         |  |                    |  |   |  |   |  |
| 9        | LEDpin<br>LED引脚          |   |  | Brass<br>黄铜         |  | 1         |  | Silvering<br>镀银    |  |   |  |   |  |
| 8        | Base<br>底座               |   |  | PA46                |  | 1         |  |                    |  |   |  |   |  |
| 7        | Pin<br>引脚                |   |  | Brass<br>黄铜         |  | 1         |  | gold-plating<br>镀金 |  |   |  |   |  |
| 6        | Contact material<br>接触材质 |   |  | silver alloy<br>银合金 |  | 1         |  | Silvering<br>镀银    |  |   |  |   |  |
| 5        | LED Base<br>LED底座        |   |  | PC<br>塑胶            |  | 1         |  |                    |  |   |  |   |  |
| 4        | Arm nut<br>固定螺帽          |   |  | Brass<br>黄铜         |  | 1         |  | nickeling<br>镀镍    |  |   |  |   |  |
| 3        | Oring<br>O型圈             |   |  | Silica gel<br>硅胶    |  | 1         |  |                    |  |   |  |   |  |
| 2        | Housing<br>外壳            |   |  | SUS<br>不锈钢          |  | 1         |  |                    |  |   |  |   |  |
| 1        | Key<br>按键                |   |  | SUS<br>不锈钢          |  | 1         |  |                    |  |   |  |   |  |
| NO<br>序号 | Part name<br>部件名         |   |  | Material<br>材料      |  | QTY<br>数量 |  | Remark<br>备注       |  |   |  |   |  |

|                                                                                                                                                          |      |          |             |                                                                                                                      |                            |      |            |        |                      |                                                                                       |                         |       |  |
|----------------------------------------------------------------------------------------------------------------------------------------------------------|------|----------|-------------|----------------------------------------------------------------------------------------------------------------------|----------------------------|------|------------|--------|----------------------|---------------------------------------------------------------------------------------|-------------------------|-------|--|
| A4                                                                                                                                                       |      |          |             |  <div>台普</div> <div>ROC CPU</div> | COMMON TOLERANCE           |      | UNIT       | MM     | PROJCTED             |  | PRODUCT NAME:           |       |  |
| A3                                                                                                                                                       |      |          |             |                                                                                                                      |                            |      | DRAWN BY   | FUYUAN | CHECKED BY           | COCO                                                                                  | MODEL NO: TP92209P224RS |       |  |
| A2                                                                                                                                                       |      |          |             |                                                                                                                      | DATE                       | 2019 | APPROVAL B | ALEN   | Https: www.rocpcu.tw |                                                                                       |                         |       |  |
| A1                                                                                                                                                       |      |          |             |                                                                                                                      | ROC CPU TECHNOLOGY CO.,LTD |      |            |        |                      |                                                                                       |                         |       |  |
| REV                                                                                                                                                      | DATE | REVISION | DESCRIPTION |                                                                                                                      |                            |      |            |        |                      |                                                                                       |                         | ISSUE |  |
| A                                                                                                                                                        |      | B        |             | C                                                                                                                    |                            | D    |            | E      |                      | F                                                                                     |                         | G     |  |
| Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission |      |          |             |                                                                                                                      |                            |      |            |        |                      |                                                                                       |                         |       |  |