







PCB. Welding diagram
PCB.焊接图



Circuit diagram
电路图



SPECIFICATION

规范
Rating: 50mA.12V DC
额定值: 50mA.12V DC
Insulation resistance: $\geq 100\text{M}\Omega$
绝缘电阻: $\geq 100\text{M}\Omega$
Dielectric strength: $\geq 250\text{V AC 1 min}$
抗电强度: $\geq 250\text{V AC 1 min}$

Contact resistance: $\leq 100\text{m}\Omega$ max
接触电阻: $\leq 100\text{m}\Omega$ max
Travel: $0.20 \pm 0.1\text{mm}$
行程: $0.20 \pm 0.1\text{mm}$
Lifetime: 200000 times
寿命: 200000 times
Operating force: $160 \pm 50\text{gf}$
操作力: $160 \pm 50\text{gf}$

6	Cover plate 盖板	SUS	1	Black 黑色
5	Stem 按钮	PAA	1	Temperature resistance of 280 耐温280℃
4	waterproofing membrane 防水膜	Silicone rubber 硅胶	1	Black heat-resistant 280 黑色耐温280℃
3	Reed 簧片	SUS	1	Silver overlay 覆银
2	Base 基座	PPA	1	Temperature resistance of 280 耐温280℃
1	Pin 引脚	Brass 黄铜	1	Silvering 镀银
NO 序号	Part name 部件名	Material 材料	QTY 数量	Remark 备注

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP16121608
DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
ROCPCU TECHNOLOGY CO.,LTD				
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				