










Schematic Diagram
电气原理图



Installation View
安装视图

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT

MM

PROJECTED



PRODUCT NAME:

DRAWN BY

FUYUAN

CHECKED BY

COCO

MODEL NO: TP91208G224GS

DATE

2019

APPROVAL B

ALEN

Https: www.rocpcu.tw

ROC PU TECHNOLOGY CO.,LTD

Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission

性能参数														
1. Heating current: Ui: AC250V, Ith: 3A 发热电流: Ui: AC250V, Ith: 3A														
2. Rated current:2A/DC36V 额定电流:2A/DC36V														
3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min														
4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ														
5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ														
6. Pressing stroke:1.80mm ± 0.10 按压行程:1.80mm ± 0.10														
7. Contact stroke:0.60mm±0.10 接触行程 :0.60mm±0.10														
8. welding temperature: 320 ℃± 20 ℃ 焊接温度: 320 ℃± 20 ℃														
9. Welding duration: Less than 3 seconds in duration 焊接时长: Less than 3 seconds in duration														
10. Nut assembly torque:5-14N 螺帽装配力矩:5-14N														
11. Protection level:IP65 防护等级:IP65														
12. Explosion prevention level: IK08 防暴等级: IK08														
13. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃														
14. Compression torque: ≤ 3N 按压扭力: ≤3N														
15. Electrical life: 100000 cycles 电气寿命: 100000 cycles														
16. mechanical: 5000000cycles 机械寿命: 5000000cycles														
17. Operation method:Self compound 操作方式: 自复式														
18. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N														
19. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下														
20. LED lamp lifespan: 40000h LED寿命: 40000h														
21. LED color: Green LED颜色: 绿色														
</														

材质参数													
9	luminous zone 发光区			PC 塑料			1						
8	LEDpin LED脚			Brass 黄铜			1		Silvering 镀银				
7	Pin 引脚			Brass 黄铜			1		gold-plating 镀金				
6	Contact material 接触材质			silver alloy 银合金			1		Silvering 镀银				
5	Base 基座			PBT			1						
4	Arm nut 固定螺帽			Brass 黄铜			1		nickeling 镀镍				
3	Oring O型圈			Silica gel 硅胶			1						
2	Housing 外壳			SUS 不锈钢			1						
1	Key 按键			SUS 不锈钢			1						
NO 序号	Part name 部件名			Material 材料			QTY 数量		Remark 备注				

A4				 ROCPCU	COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:	
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91208G224GS	
A2					X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw	
A1					X.X	± 0.15	ROCPCU TECHNOLOGY CO.,LTD					
REV	DATE	REVISION	DESCRIPTION		ISSUE	X						
							Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission					

A		B		C		D		E		F		G	
---	--	---	--	---	--	---	--	---	--	---	--	---	--