

RoHS

Specifications(规格):


- 1.Impedance(特性阻抗): 50Ω;
2.Frequency (工作频率): DC~6GHz;
3.VSWR (电压驻波比): 1.50@3GHz; 1.60@6GHz;
4.Insulation resistance(绝缘阻抗): ≥100MΩ;
5.Dielectric withstand voltage (介质耐电压): 800V AC;
6.Mating cycles (耐久性): ≥25 cycles;
7.Engagement force(啮合力): ≤ 25N;
8.Retention force latch(保持力): ≥110N;
9.Temperature range(使用温度):
-40℃~+105℃;

PART NO.:


XZ X X -K1M- XXXX -K1M- X X
① ② ③ ④ ⑤

- ① Cable TYPE:
3: RG174
4: 1.5DS
6: RG58
7: Dacar302
8: RG174LL
9: RG58LL
② Successive number: 1~Z
③ Length (mm): 1000=1000mm
④ Coding A: A~Z
⑤ Coding B: A~Z

接点表(Wiring Table)



REVISIONS				
REV.	ECN NO.	LOCATION	DESCRIPTION	DATE
A0	N/A		INITIAL RELEASE	2024.10.28



PART NO.	Length (mm/inch)	TOLERANCES (mm/inch)
XZ71-K1M-500-K1M-ZZ	500 [19.685]	±10 [0.394]
XZ71-K1M-1000-K1M-ZZ	1000 [39.370]	±15 [0.591]
XZ71-K1M-1500-K1M-ZZ	1500 [59.055]	±15 [0.591]
XZ71-K1M-2000-K1M-ZZ	2000 [78.740]	±20 [0.787]
XZ71-K1M-3000-K1M-ZZ	3000 [118.110]	±30 [1.181]
XZ71-K1M-5000-K1M-ZZ	5000 [196.851]	±60 [2.362]

2	Connector	FAKRA Male connector,Z Code	2SET	
1	Cable	RTK031 Cable PVC OD3.30 Black,-40~105℃		
NO.	NAME	SPEC.	Q'TY	NOTE

	DESIGN	希文	VIEW:	MODEL TYPE: Assembly cable, FAKRA series
	CHECKED		UNIT: mm/in	PART NO.: XZ71-K1M-XXXX-K1M-ZZ
	APPROVED		SIZE: A4	DWG NO.: X-XZ71-K1M-XXXX-K1M-ZZ
XKB INDUSTRIAL PRECISION CO.,LIMITED				SCALE: N/A
				PAGE: 1/1
				REVISION: A0