











面板最大厚度10.50 [0.413]



A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE	
X.XX	± 0.10
X.X	± 0.15
X	± 0.25
ANGULAR	—

UNIT	MM	PROJECTED	PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	MODEL NO: TP91922G124RS
DATE	2019	APPROVAL B	Https: www.rocpu.tw
ROCPU TECHNOLOGY CO.,LTD			
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission			

	A	B	C	D	E	F	G								
1	性能参数 1. Heating current: Ui: AC250V, lth: 5A 发热电流: Ui: AC250V, lth: 5A 2. Rated current:3A/DC36V 额定电流:3A/DC36V 3. Power-frequency withstand voltage:2000V1min 工频耐压:2000V1min 4. Insulation resistance:≥1000MΩ 绝缘电阻 :≥1000MΩ 5. Contact resistance:≤50mΩ 接触电阻 :≤50mΩ 6. Pressing stroke:3.00mm ± 0.10 按压行程:3.00mm ± 0.10 7. Contact stroke:1.50mm±0.10 接触行程 :1.50mm±0.10 8. Nut assembly torque:5-14N 螺帽装配力矩:5-14N 9. Protection level:IP67 防护等级:IP67 10. Explosion prevention level: IK10 防暴等级: IK10 11. Working environment temperature: -20 ℃~+55 ℃ 工作环境温度: -20 ℃~+55 ℃ 12. Compression torque: ≤ 6N 按压扭力: ≤6N			13. Electrical life: 500000 cycles 电气寿命: 500000 cycles 14. mechanical: 500000cycles 机械寿命: 500000cycles 15. Operation method:Self-locking 操作方式: 自锁式 16. NO reverse thrust foot torque: ≤30N NO反推脚扭力: ≤30N 17. LED lamp power consumption: 20m以下 LED灯功耗: 20m以下 18. LED lamp lifespan: 40000h LED寿命: 40000h 19. LED color: Red LED颜色: 红色				1							
2	连接形式 1. Welding temperature of wire: 320 ± 20 ℃ 线材焊接温度: 320±20℃ Wire welding duration: less than 3 seconds 线材焊接时长: 时长3秒以下 2. Can be used with dedicated connectors: 可配专用接插件使用: 2.1 1NO1NCSwitch function wire: green (C) blue wire (NO) yellow wire (NC) 1NO1NC开关功能线材: 绿色(C) 蓝线 (NO) 黄线 (NC) 2.2 2NO2NC switch function wire: green black wire (C), blue black wire (NO), yellow white wire (NC) 2NO2NC开关功能线材: 绿黑线 (C)、蓝黑线 (NO)、黄白线(NC) 2.3 LED functional wire: red wire positive pole, black wire negative pole, LED without distinction between positive and negative poles LED功能线材: 红线正极, 黑线负极, LED不分正负极							2							
3	台普 ROCPU			COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:	5				
						DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91922G124RS					
				X.XX	± 0.10	DATE	2019	APPROVAL B	ALEN	Https: www.rocpu.tw					
				X.X	± 0.15	ROCPU TECHNOLOGY CO.,LTD									
				X	± 0.25										
				X	± 0.25	Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission									
				ANGULAR	——										
4	A			B		C		D		E		F		G	
5	REV			DATE		REVISION		DESCRIPTION		ISSUE					

A		B		C		D		E		F		G	
材质参数													
10	luminous zone 发光区			PC 塑料		1							
9	LEDpin LED脚			Brass 黄铜		1		Silvering 镀银					
8	Base 底座			PA46		1							
7	Pin 引脚			Brass 黄铜		1		gold-plating 镀金					
6	Contact material 接触材质			silver alloy 银合金		1		Silvering 镀银					
5	LED Base LED基座			PC 塑料		1							
4	Arm nut 固定螺帽			Brass 黄铜		1		nickeling 镀镍					
3	Oring O型圈			Silica gel 硅胶		1							
2	Housing 外壳			SUS 不锈钢		1							
1	Key 按键			SUS 不锈钢		1							
NO 序号	Part name 部件名			Material 材料		QTY 数量		Remark 备注					

A4				 台普 ROCPS	COMMON TOLERANCE		UNIT	MM	PROJCTED		PRODUCT NAME:		
A3							DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP91922G124RS		
A2					DATE	2019	APPROVAL B	ALEN	Https: www.rocpsu.tw				
A1					ROCPS TECHNOLOGY CO.,LTD								
REV	DATE	REVISION	DESCRIPTION									ISSUE	
A		B		C		D		E		F		G	
Copies are issued in strict confidence and shall not be reproduced or copied,or used as the basic of manufacture or sale of apparatus without permission													