

NOTE:

1.MATERIAL:

a.HOUSING:PA46 UL94 V-0 BLACK

b.CONTACT: SUS304 T=0.35MM


(SURFACE PLATING: Au1u")

SEE ORDERING INFORMATION

2.ELECTRIC:


a.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE

b.OPERATING TEMPERATURE: $-25^{\circ}\text{C}\sim +85^{\circ}\text{C}$



PCB Layout Diagram

TOP View



3	TERMINAL(+)	1	SUS304 T=0.35MM	Au(1u")-Plating
2	TERMINAL(-)	1	SUS304 T=0.35MM	Au(1u")-Plating
1	HOUSING	1	PA46 UL94 V-0	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

_____		new			2015/5/3		A		瀚源
ECN BO.		DESCRIPTION.			DATE.		REV.		
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER				SCALT: 1/2		SCALE: 3:1
Mikey	Tom	Jerry	PART NAME	BH-18650-4	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X. ±0.25		
			MODEL NAME	BH-18650-4			X.x ±0.20		
			3RD ANGLE PROJ	HanElectricity Co.,LTD				X.xx ±0.15	
			FILE.NO.						