

Specifications(规格):



- 1.Impedance(特性阻抗) : 100Ω;
- 2.Frequency (工作频率) : DC~2GHz;
- 3.Return Loss (回波损耗) : ≥ 20dB @1GHz;
- 4.Insulation resistance(绝缘阻抗) : ≥100MΩ;
- 5.Dielectric withstand voltage (介质耐电压) : 250V AC;
- 6.Mating cycles (耐久性) : ≥25 cycles;
- 7.Retention force latch(保持力) : ≥110N;
- 8.Temperature range(使用温度): -40℃~+105℃;

PART NO.:

XZ 5 X - H14FR- XXXX -H14F-X X
①② ③ ④⑤

- ① Cable Type: HSD 535;
- ② Successive number: 1~Z;
- ③ Length(mm): 1000=1000mm
- ④ Coding A: A~Z
- ⑤ Coding B: A~Z

Wiring Table



3	Connector	HSD4P Female right angle connecto, Z Code	1 SET		XKB星野 Connection						
2	Connector	HSD4P Female connecto, Z Code	1 SET			DESIGN	Sivan	VIEW: 	MODEL TYPE: Assembly Cable:HSD4Pin Series		
1	Cable	LEONI Dacor® 535 Cable PVC ODø4.6±0.3mm Black	1 PCS	DACAR		CHECKED		UNIT: mm/in	PART NO.: X252-H14FR-XXXX-H14F-ZZ		
						APPROVED		SIZE: A4	DWG NO.: X-X252-H14FR-XXXX-H14F-ZZ		
NO.	Name	SPEC.	QTY	NOTE	KKB INDUSTRIAL PRECISION CO., LIMITED				SCALE	PAGE	REVISION
					www.helloxb.com				N/A	1/1	A0