

产 品 基 本 参 数

安倍:20A 电压:300V 线径:0.2-2.5mm²

胶壳: 尼龙66工程塑料, UL 94V-0阻燃等级





温度: 110° C (UL),-40° C to T110° C(IEC)

触点材料: 黄铜 (HPb59-3), 镀镍


脚子: 黄铜 (H65) 环保

推荐剥线长度: 6-7mm

接线位数: 2位-24位



PCB LAYOUT



		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	HY128-5.08-XXP	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X. ±0.25		
			MODEL NAME	HY128-5.08-XXP			X.x ±0.20		
			3RD ANGLE PROJ		HanElectricity Co.,LTD				FILE.NO.