

REVISIONS				DATE	DESIGN
REV.	ECN NO.	LOCATION	DESCRIPTION	INITIAL RELEASE	
A0	N/A			2024.10.31	

- Specifications(规格):
- 1.Impedance(特性阻抗) : 50Ω;
 - 2.Frequency (工作频率) : DC~6GHz;
 - 3.VSWR (电压驻波比) : 1.50@3GHz;
 - 4.Insulation resistance(绝缘阻抗) : ≥100MΩ;
 - 5.Dielectric withstand voltage (介质耐电压) : 800V AC;
 - 6.Mating cycles (耐久性) : ≥5 cycles;
 - 7.Engagement force(啮合力) : ≤45N;
 - 8.Retention force latch(保持力) : ≥110N;
 - 9.Temperature range(使用温度): -40℃~+105℃;

PART NO.:

X Z X 1 -K1F- XXXX -K1FRW- X X
① ② ③ ④ ⑤

- ① Cable TYPE:
3: RG174
4: 1.5DS
7: Dacar302
8: RG174LL




- ② Successive number: 1~Z
③ Length (mm): 1000=1000mm
④ Coding A: A~Z
⑤ Coding B: A~Z

接点表(Wiring Table)

A端(A port)

Cable

B端(B port)



防水等级:
IP67

4	Tube	Heat Shrinkable Tube Waterproof	1PC	
3	Connector	FAKRA Female connector R/A Waterproof,Z Code	1SET	
2	Connector	FAKRA Female connector,Z Code	1SET	
1	Cable	RG174LL Cable PVC OD2.80mm Black,-40~105℃		
NO.	NAME	SPEC.	Q'TY	NOTE

CONNEXION

希文

DESIGN

CHECKED

APPROVED

VIEW:

UNIT: mm/in

SIZE: A4

MODEL TYPE:

PART NO.:

DWG NO.:

SCALE

PAGE

REVISION

www.helloxkb.com

www.xk-dg.com

XKB INDUSTRIAL PRECISION CO.,LIMITED

N/A

1/1

A0