







P.C.B LAYOUT TOP VIEW




SCHEMATIC



技术要求

- 1、插入力: 2.94~29.4N (0.3~3.0kgf)
- 2、拔出力: 2.94~29.4N (0.3~3.0kgf)
- 3、接触电阻: $\leq 50\text{m}\Omega$
- 4、绝缘电阻: $>100\text{M}\Omega$ DC 500V
- 5、耐电压: AC 500V 1min无飞弧及击穿
- 6、寿命: 5000 10~20次/min
- 7、额定负载: DC 30V 0.5A
- 8、适用温度范围: $-25\sim 85^{\circ}\text{C}$
- 9、推荐使用插头:



DC-002-XX

中心针直径 (mm) : 1.0, 1.1, 1.3, 1.65

序号	零件料号	名称	材料	数量	镀层/颜色	备注
1		塑料	PBT	1PCS	黑色	
2		盖子	PBT	1PCS	黑色	
3		弹片	锰钢=0.25	1PCS	镀锡	
4		弯钩	铁 =0.3	1PCS	镀锡	
5		平片	铁 =0.3	1PCS	镀锡	
6		圆针	铁	1PCS	镀锡	

_____		new		2015/5/3		A		瀚源	
ECN BO.		DESCRIPTION.		DATE.		REV.			
DESIGNED	CHECKED	APPROVAL	DRAWING NUMBER			SCALT: 1/2		SCALE: 3:1	
Mikey	Tom	Jerry	PART NAME	DC-002-XX	UNLESS OTHERWISE SPECIFIED,TOLERANCE:		X.	±0.25	
			MODEL NAME	DC-002-XX			X.x	±0.20	
			3RD ANGLE PROJ	HanElectricity Co.,LTD		X.xx	±0.15	ANGULAR	±3°
							FILE.NO.		