








REV.	ECN NO.	DATE	SIGN	DESCRIPTION
A		2020/09/16	Jone	Change Rev 01 To Issue Rev A



Note:

- Waterproof Rate: IP68
(No Ingress of Dust/ Protected Against Harmful Effects Caused in 1 Meter Water Within 24 Hours)
- Temperature Range: -40°C to +90°C
- Current Rating: 2A
- Max. Panel Thickness 4.5mm(Without Cap Chain)
- Material:
Housing: Nylon, Black
Pin: Copper Alloy, Gold Plated
O-Ring: Rubber
Screw Nut: Zinc Alloy, Nickel Plated
Shell: Zinc Alloy, Nickel Plated



Pin Assignments Front View

PCB Layout

Recommended Panel Cut-Out

ODS 歐德斯電通科技股份有限公司				
TITLE SENSOR, M12, PANEL M CONN. M PIN, SCREW				
QC : QC check		DSGN Reg	PART NO. MDAPM08MBB-SHP8001	
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°	UNIT: mm	SCALE 1 : 1	DWN. Jone	DATE 2020/09/16
SHEET 1 of 1		SIZE A4	CHKD. Miller	DATE 2020/09/16
		REV. A	APVD. Reg	DATE 2020/09/16