






AFTER MATING








Waterproof Ring

**G-Switch USB-C Specification:**

- 1.Current rated: 5A on vbus/1.25A on vconn/0.25A on other
- 2.Withstanding voltage: 100V AC/minute
- 3.Contact resistance: 40mΩ Max
- 4.Insulation resistance: 100MΩ Min
- 5.Operating temperature: -40°C ~ +85°C
- 6.Mating force: 5N~20N
- 7.Unmating force: 8N~20N
- 8.Durability cycle:10,000 cycles
- 9.Waterproof grade: IP-X7.
- 10.Compliant with: IEC62680-1-3

A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND			VBUS	CC1	D+	D-	SBU1	VBUS			GND
First			First	Second	Second	Second	Second	First			First

B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
GND			VBUS	SBU2	D-	D+	CC2	VBUS			GND
First			First	Second	Second	Second	Second	First			First

RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05

NO.	PARTS	MATERIAL	REMARKS
1	SHELL	ZINC ALLOY	Ni30u"MIN PLATED
2	GND PLATE	STAINLESS STEEL304	---
3	MID PLATE	STAINLESS STEEL301	---
4	HOUSING	HIGH TEMPERATURE PLASTIC	PA9T BLACK UL 94 V-0
5	TERMINALS	COPPER ALLOY C7025	Au1u"MIN PLATING ON CONTACT AREA Tin30u"MIN PLATING ON SOLDER AREA
6	RUBBER	SILICA GEL	RED

**RoHS**
Compliant
EU RoHS StandardsSCALE: 1:1 UNIT: mm
SIZE: A4Unless otherwise
General Tolerance:
X.xx ±0.30
X.xxx ±0.20
X.xxx ±0.10
X.x" ±3°
X.xx" ±2°Title: IPX7 Horizontal Type-c 16P Female
SMT Mid-Mount 1.6 L=6.7mm

Molde Code: GT-USB-9103E

DRAWN	CHECKED	APPROVED	DATE
Xia	Chen	Chen	2023.02.01

品赞科技
www.dg-switch.com

REV: A0 SHEET: 1/1