

A

B

C

D

E

F

G

A

B









C

D


E

F

G



Recommended PCB mounting pattern and metal mask dimensions
Recommended metal mask thickness: t=0.1



Recommended FPC/FFC Dimensions

NOTE:

1. MATERIAL:

HOUSING: LCP COLOR: NATURAL.

CONTACTS: COPPER ALLOY.

PEG: COPPER ALLOY.

ACTUATOR: LCP OR PA. COLOR:BLACK

2. RATING:

OPERATING VOLTAGE: 50Vrms AC.

CURRENT RATING: 0.5A.

OPERATING TEMPERATURE: -55°C~+85°C.

OPERATING HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)

STORAGE TEMPERATURE RANGE: -10°C~+50°C.

STORAGE HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)

2	端子	铜	点镀金	
1	底座	LCP	本色	
序号	品名	材质	电镀/颜色	备注




深圳市虹成电子有限公司

品名	FPC座
TITLE	
料号	HC-FPC-0.5-6P-FHH10
PART NO	

GENERAL TOLERANCES
(UNLESS SPECIFIED)

比列
SCALE

1:1



X.X : ±0.30 X.X' : ±5'

单位
UNIT

MM

制图
DRAW

AhYe

X.XX : ±0.20 X.XX' : ±2'

张数
PART NO

1 OF 1

审核
CHECKED

夏操云

版本
REV

A

批准
APPROVE

赵亮亮

