

A

B

C

D

E

F

G

A

B






C

D




E

F


G



NOTE:
1. MATERIAL:
HOUSING: LCP COLOR: NATURAL.
CONTACTS: COPPER ALLOY.
PEG: COPPER ALLOY.
ACTUATOR: LCP OR PA. COLOR: BLACK
2. RATING:
OPERATING VOLTAGE: 50Vrms AC.
CURRENT RATING: 0.5A.
OPERATING TEMPERATURE: $-55^{\circ}\text{C} \sim +85^{\circ}\text{C}$.
OPERATING HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)
STORAGE TEMPERATURE RANGE: $-10^{\circ}\text{C} \sim +50^{\circ}\text{C}$.
STORAGE HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)




Recommended PCB mounting pattern and metal mask dimensions
Recommended metal mask thickness: $t=0.1$



Recommended FPC/FFC Dimensions

2	端子	铜	点镀金	
1	底座	LCP	本色	
序号	品名	材质	电镀/颜色	备注

 深圳市虹成电子有限公司		品名	FPC座	
		TITLE		
		料号	HC-FPC-0.5-30P-FHH10	
		PART NO		
GENERAL TOLERANCES (UNLESS SPECIFIED)		比列	1:1	
SCALE		单位	MM	制图
X.X : ± 0.30 X.X' : $\pm 5^{\circ}$		张数	1 OF 1	AhYe
X.XX : ± 0.20 X.XX' : $\pm 2^{\circ}$		PART NO	CHECKED	夏操云
版本		REV	A	批准
			APPROVE	赵亮亮

