

A

B

C

D

E

F

G

A

B






C

D




E

F


G



NOTE:
1. MATERIAL:
HOUSING: LCP COLOR: NATURAL.
CONTACTS: COPPER ALLOY.
PEG: COPPER ALLOY.
ACTUATOR: LCP OR PA. COLOR: BLACK
2. RATING:
OPERATING VOLTAGE: 50Vrms AC.
CURRENT RATING: 0.5A.
OPERATING TEMPERATURE: -55°C~+85°C.
OPERATING HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)
STORAGE TEMPERATURE RANGE: -10°C~+50°C.
STORAGE HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)




Recommended PCB mounting pattern and metal mask dimensions
Recommended metal mask thickness: t=0.1



Recommended FPC/FFC Dimensions

2	端子	铜	点镀金	
1	底座	LCP	本色	
序号	品名	材质	电镀/颜色	备注

 深圳市虹成电子有限公司		品名	FPC座	
		TITLE		
		料号	HC-FPC-0.5-10P-FHH10	
		PART NO		
GENERAL TOLERANCES (UNLESS SPECIFIED)		比列	1:1	
		SCALE		
X.X : ±0.30 X.X' : ±5'		单位	MM	制图
		UNIT		
X.XX : ±0.20 X.XX' : ±2'		张数	1 OF 1	审核
		PART NO		
		版本	A	批准
		REV		
		制图	AhYe	夏操云
		DRAW		
		审核	夏操云	赵亮亮
		CHECKED		
		批准	赵亮亮	
		APPROVE		