

D

1. 塑件表面应光洁、无毛边、无明显收缩、缺陷、裂纹等现象。(The surface of the plastic parts should be smooth, no rough edges, no obvious shrinkage, defects, cracks and other phenomena.)
2. 温度范围(Temperature range): $-25^{\circ}\text{C}\sim 85^{\circ}\text{C}$.
3. 额定电压(Rated voltage): 50V, AC/DC(=等效).
4. 接触电阻(Contact resistance): $\leq 0.03\Omega$.
5. 绝缘电阻(Insulation resistance): $\geq 500\text{M}\Omega$.

FG