

A

B

C

D

E

F

G

A

B






C

D




E

F


G



NOTE:
1. MATERIAL:
HOUSING: LCP COLOR: NATURAL.
CONTACTS: COPPER ALLOY.
PEG: COPPER ALLOY.
ACTUATOR: LCP OR PA. COLOR: BLACK
2. RATING:
OPERATING VOLTAGE: 50Vrms AC.
CURRENT RATING: 0.5A.
OPERATING TEMPERATURE: -55°C~+85°C.
OPERATING HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)
STORAGE TEMPERATURE RANGE: -10°C~+50°C.
STORAGE HUMIDITY RANGE: RELATIVE HUMIDITY 90% MAX.(NO CONDENSATION)




Recommended PCB mounting pattern and metal mask dimensions
Recommended metal mask thickness: t=0.1



Recommended FPC/FFC Dimensions

2	端子	铜	点镀金	
1	底座	LCP	本色	
序号	品名	材质	电镀/颜色	备注

 深圳市虹成电子有限公司		品 名 TITLE		FPC座		
		料 号 PART NO		HC-FPC-0.5-7P-FHH10		
GENERAL TOLERANCES (UNLESS SPECIFIED)		比 列 SCALE	1 : 1			
X.X : ±0.30 X.X* : ±5°		单 位 UNIT	MM	制 图 DRAW	AhYe	
X.XX : ±0.20 X.XX* : ±2°		张 数 PART NO	1 OF 1	审 核 CHECKED	夏操云	
		版 本 REV	A	批 准 APPROVE	赵亮亮	