





REV.	ECN NO.	REVISED	DATE



技术要求:

- 1、截断面毛刺高度 $\leq 0.03\text{mm}$;
- 2、部件要求平整,无变形、裂纹、损伤等外观缺陷;

1	TERMINAL	1	SUS304 T=0.15MM	Ni-Plating
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com							
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10		ANGLES: X :±1° X.X :±0.5°		DSND	WangHeng	DATE	2024-12-16	TITLE:	
				CHKD	ZhouRuicai	DATE	2024-12-16	电池扣AG10 铆接式 Ni	
				APVD	XueShunYong	DATE	2024-12-16	PART NO.:	
WEIGHT:		SCALE:		SIZE: A4		VIEW: 		MY-AG10-02-J	
SHEET 1 OF 1		UNIT: mm		REV.: A/0		OBJECT: MY		DRAW NO.:WD-CP-0437	