






REV.	ECN NO.	REVISED	DATE



工程部
2024-12-16
H. WANG

技术要求:

- 截剪断面毛刺高度 $\leq 0.03\text{mm}$;
- 部件要求平整,无变形、裂纹、损伤等外观缺陷;

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com			
DECIMALS:	ANGLES:	DSND	WangHeng	DATE	2024-12-16
X :±0.30	X :±1°	CHKD	ZhouRuicai	DATE	2024-12-16
X.X :±0.25	X.X :±0.5°	APVD	XueShunrong	DATE	2024-12-16
X.XX :±0.20		WEIGHT:	SCALE:	SIZE: A4	VIEW:
X.XXX :±0.10		SHEET 1 OF 1	UNIT: mm	REV.: A/0	OBJECT: MY
				TITLE: 电池扣AG10 铆接式带触发片 Ni	
				PART NO.: MY-AG10-03-J	
				DRAW NO.:WD-CP-0438	

1	TERMINAL	1	SUS304 T=0.15MM	Ni-Plating
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR